# Biolase WaterLase iPlus All Tissue Laser



Rating: 4.0 **Price:** Variant price modifier:

Price with discount:

Salesprice with discount:

USD 10,850.00

Discount:

In Stock

Ask a question about this product

Manufacturer: Biolase

Description

Biolase WaterLase iPlus All Tissue Laser

## Features

iPlus Breaks the Dental Speed Barrier

- Faster than the drill, without the delay of anesthetic
- Patented laser technology delivers 10 watts of power
- Up to 100 pulses/sec. for superior soft-tissue cutting

- Enables multi-quadrant same-day procedures

iPlus is Easy to Use with its Intuitive Graphical User Interface

- For example performing a Class I Cavity Prep the iPlus™ is as easy as 1,2,3... Step 1: Select "Restorative" from the first screen Step 2: Choose "Class I" from the next screen that appears automatically Step 3: Specify any other concerns such as patient sensitivity or bond strength.Roger Levin

iPlus Provides Great Return on Investment

- A fantastic tool to increase production!" Roger Levin
- Increases treatment acceptance of day-to-day restorative cases
- Attracts new patients
- Increases productivity and enables new procedures.

iPlus Enables Painless Biological Dentistry

- Painless ,no shot necessary
- No micro-fractures or thermal damage
- NO cross contamination as with bur
- More precise, minimally invasive

iPlus includes iLase 940nm Diode Laser Docking Station

- Adds dual wavelength versatility and convenience
- First totally wireless dental laser
- 5 Watts peak power with ComfortPulse™
- Battery operated with finger switch activation
- Exclusive bendable tips in many diameters & lengths
- Single use for NO cross contamination

## Specifications

## DIMENSIONS (W X L X H)

- Uni: 11 x 19 x 33 in (28 x 48 x 84cm)
- With Fibe: 11 x 19 x 40 in (28 x 48 x 102 cm)
- Weight: 75 lbs (34 kg)

## ELECTRICAL

- Operating Voltage: 100 VAC  $\pm$  10% / 230VAC  $\pm$  10%
- Frequency: 50 / 60 Hz
- Current rating: 15.0 A / 8A
- Main control: Circuit breaker
- On / Off control: Keyswitch
- Remote interruption: Remote interlock connector

#### WATER SPRAY

- Water type: Distilled or Sterile
- External air source: 80 120 psi. (5.5 8.2 bar)
- Water: 0 100%
- Air: 0 100%
- Interaction zone: 0.5 5.0 mm from handpiece tip to target

## OPTICAL

- Laser classification: 4
- Medium: Er, Cr:YSGG (Erbium, Chromium, Yttrium, Scandium, Gallium Garnet)
- Wavelength: 2.78 µm (2780nm)
- Frequency: 5 100 Hz
- Average power: 0.1 10.0 W
- Power accuracy: ± 20%
- Pulse energy: 0 600 mJ
- Pulse duration for "H" mode: 60 µs
- Pulse duration "S" mode: 700 µs
- Handpiece head angles: 70° contra-angle
- Gold HP tip diameter range: 200 1200 µm
- Turbo tip focal diameter range: 500-1100 µm
- Output divergence: = 8° per side
- Mode: Multimode
- Aiming Beam: 635nm (red) laser, 1mW max (safety classification 1)\*

- Water Level Sensor Beam: 635nm laser, 1mW max (safety classification 1)

- Nominal Ocular Hazard Distance (NOHD): 5cm

Comes with 2 HandPieces (TURBO & GOLD)